

AQ-710

Alkaline Aqueous Cleaner

AQ-710 is a high performance cleaner for a broad spectrum of soils. A low-foaming allpurpose glycol-free alkaline cleaning solution with a unique blend of surfactants and corrosion inhibitors, it meets or exceeds the specifications for most aerospace applications for aqueous and alkaline cleaners.

AQ-710 is designed for immersion, ultrasonic and spray applications, and is safe for use on most metals. It is non-aggressive towards aluminum, magnesium and titanium alloys, and can be used in concentrations up to 25 percent. It is moderately alkaline with low foaming levels for use in spray applications, contains inhibitors to protect metal surfaces from corrosion and it is also tolerant of hard water.

Designed as a high-performance cleaner on aluminum, anodized aluminum, brass, bronze, carbon steel, stainless steel, cast iron, copper, magnesium, nickel, super alloys and plated metals, it also works well on titanium.

AQ-710 is excellent at removing water-soluble oils, machining fluid, synthetic coolants, medium weight and lube oils, motor oils, buffing compounds and heavy petroleum oils. It is also effective on carbonized soils.

AQ-710 is formulated with soil-rejecting properties, which suspend the solids in the cleaner after lifting them from the test material. When the soils have settled out and lighter greases coalesce and float, the cleaner solution can be filtered and skimmed, extended the effective lifespan of the cleaner significantly beyond an emulsion type cleaner.

SPECIFICATIONS COMPLIANCE

- ASTM F 1110
- ASTM F 1111
- AMS 1551A Class 2*
- ARP 1511
- ARP 1755B
- ASTM F519*
- ASTM F945 Method A
- GEAE Method 22, 51145*
- Honeywell C 148
- PWA 36604-Hot Corrosion*, Non-Metallic*, Stock Loss, Stress Corrosion
- PWA 407 Rubber*
- RR CSS 204 Type A*
- SCAQMD*

*Approval is pending

BENEFITS

- Alkaline cleaner
- SCAQMD Clean Air Certified*
- Low foam level
- Rust inhibitor
- Works on a wide range of materials
- Cleans a broad spectrum of soils



APPLICATIONS

Cleaning methods:

- Dipping / immersion cleaning
- Ultrasonic cleaning

Ideal for:

- Aluminum
- Anodized aluminum
- Brass and bronze
- Carbon steel
- Cast iron
- Stainless steel
- Copper
- Magnesium
- Nickel
- Super alloys
- Plated metals
- Titanium

Applications:

Excellent Carbon Steel & Cast Iron Bronze Good • • • Stainless Steel Nickel & Superalloys Pt) Magnesium Fair •• Anodized Aluminum Cr, Ir, I Aluminum Titanium Platting ø Copper Poor . Brass a , Cd, Zinc Not Recommended Water-Soluble Oils • • • ••• •••• • • • • •••• ••• Machining Fluid Synthetic Coolants • • • • •••• •••• ••• •••• •••• ••• Medium Weight Oils ••• Lube Oils •••• • • • • • • • • •••• •••• ••• •••• •••• • • • • ••• **Buffing Compounds** • • • • • • • • •••• ••• Motor Oils • • • • • • • • •••• • • • • •••• ••• ... Heavy Petroleum Oils • • • • • • • • • • • • ••• ... Carbonized Soils ••• •• •• Railroad & Axel Grease Glues Spray Adhesives

Removes:

- Buffing compounds
- Carbonized soils
- Cutting fluids
- Heavy oils and dirt
- Lubricant oils
- Machine oils
- Machining fluid
- Medium weight and lube oil
- Motor oil
- Synthetic coolant
- Water-soluble oils



PROPERTIES

pH Level	Alkaline
Foam Level	Low
Silicates	Yes
Phosphates	No
Hard Water Tolerance	Moderate
Aerospace Compliant	Yes
SCAQMD Certified	Pending

USE RECOMMENDATIONS

Cleaning Method	Concentration	Temp.	Typical Duration
Immersion	3–25%	80–180°F / 27–82°C	2–30 mins
Ultrasonic	3–25%	80–180°F / 27–82°C	2–30 mins
Spray	1–12% Recomm.: 2–5%	130–180°F / 54–82°C	0.25–3 mins
Steam	1–12%	150–200°F / 66–93°C	1–5 mins

PACKAGING

55 gal / 208 L drum 5 gal / 20 L pail

INSTRUCTIONS FOR USE

Dilute cleaner with water to the appropriate concentration or use. Cleaning efficiency can be improved with agitation and heat. Increasing cleaning bath temperature will decrease foaming.

Maintenance Recommendations

Maintain cleaning bath by skimming and/or filtering. Check in-use cleaner concentration to maintain cleaning effectiveness. The recommended method for measuring concentration is titration method.

Concentration Verification: HACH Alkalinity Titration Kit*

Titrant	0.5N Sulfuric Acid
Indicator	Bromcresol Green-Methyl Red
Concen- tration %	Titrant drops x 1.43

* Ordering info: Alkalinity Test Kit, Model AL-TA; Product# 2314500; Mfr. Hach Company; Website www.hach.com

HEALTH AND SAFETY

Review all relevant health and safety information before using this product. For complete health and safety information, refer to the product Safety Data Sheet, which is available at **www.magnaflux.com**.